SEP 60 RAIL Single Use Condensate Cleaner





Before Starting Assembly, please read the following:

SEP 60 is a single-use product. It should be replaced as directed to ensure its vital environmental and legally protective functions are performed correctly.

SEP 60 has been designed to clean condensate from a compressor system of up to 60cfm (1.7m3min) to better than 5ppm oil-in-water; suitable for discharge to a sewer. **Note:** This is generally well below the accepted level, but it is the users responsibility to ensure compliance with local regulations.



prefer this fitting.

Please Note

The unit comes shipped with a 6mm inlet port as standard

We can also supply a 1/4" inlet as an option.

Please state when ordering if you would

installation



Fix the wall plate vertically on a suitable wall or the compressor cabinet. Isolate the compressor and look out for cables and pipes when drilling.



Slide the SEP60 on to the plate, with the venting flutes at the top.



Connect all drain points, insert tube into push fitting in the inlet (top).

- 6mm tube for metric
- 1/4" tube for imperial



Connect tube into outlet fitting and feed to drain (side). Ensure a steady fall from outlet point to drain with no kinks or tight bends.

- 10mm tube for metric
- \bullet 3/8" tube for imperial

Important Always use an automatic drain. Set timers to short open periods of one second or less.

NEVER use manual drains which could flood the separator, forcing partially treated or untreated condensate to be discharged.





SEP60 RAIL

replacement



Ensure the condensate drain(s) are switched off.

Disconnect inlet and outlet tubes from their quick fittings



Lift SEP 60 from the wall plate.



Push fit the retained disposal lid (that came with your kit) onto the top of the unit.



Insert transit plug into outlet. (this comes with each kit)

Please note this is designed to create a tight seal and cannot be removed once inserted.



Unit is now sealed for transport to a licensed waste disposal site.

Refit the new SEP 60 to the existing wall plate and connect as before.

the SEPURA™ range

Condensate Separators to suit your requirements





t: **+44** (0)1543 379212 e: sales@sepura-technologies.com

www.sep60-rail.com











